

# Kontakt IPA PLUS

High-quality isopropyl alcohol, designed with professionals and technology enthusiasts in mind. With a main ingredient content of at least 99.7%, it ensures effective removal of contaminants without leaving any traces. It is ideal for cleaning various electronic devices due to its chemically neutral formula. It removes even tough dirt without leaving streaks or stains. Its quick-drying properties ensure that devices are ready for use in a short time, providing safety and protection for electronics.

**Product features:**

- ✓ high cleaning efficiency,
- ✓ versatility of applications,
- ✓ chemical neutrality,
- ✓ quick drying,
- ✓ variety of application forms,
- ✓ leaves no residue.

**Application:**

- ✓ CD-ROM, DVD, Audio-CD readers,
- ✓ cleaning tools, flow meters, screens, PCB boards,
- ✓ photo CD devices,
- ✓ cleaning screens,
- ✓ AV mechanisms and heads,
- ✓ ultrasonic cleaners,
- ✓ fiber optic connectors.



Physicochemical properties	
Appearance	Clear colorless liquid
Odour	Characteristic
Color	Max. 10 Pt-Co
Density at 20°C	Min. 0.79 g/cm <sup>3</sup>
Main ingredient content	Min. 99.7%
Acidity as acetic acid	Max. 0.01%
Distillation IBP	Min. 82.0°C
Shelflife	3 years

### Compatibility:

Kontakt IPA PLUS is chemically neutral towards most materials, making it safe to use on a wide range of devices, from delicate electronic components to hard metal surfaces. Its neutrality prevents the risk of damage, corrosion, or undesirable aesthetic changes, making it an ideal solution for maintaining cleanliness in various technological environments.

Application method	
Aerosol	Yes
Aerosol with brush	Yes
Applicator	Yes
Atomizer	Yes
Sprinkler	Yes
Bottle/ Canister	Yes

### Usage instructions:

**Restricted to professional users. Read SDS carefully prior to use.**

Whether you choose the liquid or aerosol version, always ensure that the device is turned off. You can apply the product directly to the surface to be cleaned or use a lint-free cloth. Allow it to dry quickly to enjoy uncompromised cleanliness.

Package	
<b>Aerosol</b>	60 ml (ART.AGT-005) - 12 pcs.* 300 ml (ART.AGT-006) - 12 pcs.* 600 ml (ART.AGT-202) - 12 pcs.*
<b>Aerosol with brush</b>	400 ml (ART.AGT-225) - 12 pcs.*
<b>Applicator</b>	50 ml (ART.AGT-001) - 12 pcs.* 100 ml (ART.AGT-002) - 12 pcs.*
<b>Atomizer</b>	250 ml (ART.AGT-267) - 12 pcs.*
<b>Sprinkler</b>	500 ml (ART.AGT-252) - 8 pcs.*
<b>Bottle/ Canister</b>	500 ml (ART.AGT-105) - 8 pcs.* 1 l (ART.AGT-003) - 10 pcs.* 5 l (ART.AGT-004) - 1 pcs.* 5 l (ART.AGT-218) - 1 pcs.* 20 l (ART.AGT-236) - 1 pcs.*

\*Quantity of pcs. in a bulk packag

### Warehousing:

Store in sealed containers in dry and well ventilated areas away from sources of heat and ignition and direct sunlight. Do not expose to temperatures exceeding 30°C. Protect against electrostatic discharge.

### Technical support:

AG TermoPasty provides technical support, answering questions about the technical specifications and applications of our products. Please contact us via email at [info@termopasty.pl](mailto:info@termopasty.pl).

### Note:

The data presented in this document reflect our current state of knowledge and describe the typical properties and applications of the product. However, the responsibility for determining the suitability of this product for specific applications lies with the user. AG TermoPasty is not liable for the results of the product's use, as the conditions of its application are beyond our control.

